

HOLOGRAPHIC

SPECIFICATIONS

Composition	्रं Avarage Thickness	Carrier	& Certifications		
	105 microns	Adhesive polyester	REACH n° 1907/2006/EU		
Hologram Skin			VEGANOK AZIENDA N. 1004		

APPLICATION INSTRUCTIONS

⊘ Applies on	SUGGESTED CUTTING SETTINGS			TRANSFER SETTINGS			
cotton, polyester, poly/ cotton blends (not suited for treated	Blade	<u></u> Pressure	>> Speed	Time	Temperature	Pressure	Peel
`and dye sublimated textiles)	45°	from 90gf with a knew knife - 130gf used knife	20 cm/sec	15 seconds	155°C (311°F)	Medium (2,5/3,5 bar)	cold

- → Mirror cut the design
- → Weed excess material
- > Place the design on the garment
- → Heat apply at the conditions shown above
- → Peel carrier cold

PRODUCT HIGHLIGHTS

- \rightarrow easy to cut and weed
- → Perfect to recreate rhinestones effect
- → intense shiny colors
 - $oldsymbol{\mathcal{L}}$ NOTE: We highly recommend to perform a test before launching a production.

CARE AND WASHING RECOMMENDATIONS

₩ Washing	Ironing	Tumble dry	Ony cleaning	Storage Shelf Life	Storage Temperature	Storage Conditions	⊲ ⊳ Position
Up to 40°C, inside-out	YES, inside-out	NO	NO	Up to 2 years	Between 18°C and 26°C	Away from sunlight and dust	Vertical

- → Wait 24 hours after the application before the first wash
- → Respect the textile recommendations
- → Do not bleach or use aggressive chemical agents

This document can be subject to variations. Updated versions are available on www.siser.com For further information, please contact our sales office: info@siser.it



Siser s.r.l. Viale della Tecnica, 18 36100 Vicenza - Italy Tel. +39 0444.287960 Fax +39 0444.287959 info@siser.it www.siser.com

r.e.a. vi 171856 reg. imp. vi n° 14971 c.s. € 103.300 i.v. p.iva 01591490246



